

Square Overflow 01007CP







Includes built-in Easily remove test membrane membrane after test overflow plate.

Snap-on No screws

NOTE:

CONTACT WATCO WITH NAME OF MANUFACTURER AND TUB MODEL NUMBER SO CORRECT LENGTH OF FLEX TUBING CAN BE OBTAINED.



PRESFLO® (PF) and Foot Actuated (FA) only

See price list for complete item number and available options.

When ordering, please specify complete catalog number and option codes.

www.watcomfg.com



For more information, contact:

WATCO Manufacturing Company 1220 South Powell Road Independence, MO 64057-2724 Ph. 816-796-3900 • 800-821-8576 Fax 816-796-0875 • 800-399-2826

WatcoFlex®

SPECIFICATIONS

WatcoFlex® Features and Benefits:

- Eliminates four Schedule 40 solvent-weld field joints. resulting in significant installed-cost savings.
- Designed with a direct drain layout, which can be easier and faster to install.
- All joints are factory sealed and tested; no solvent weld.
- · Eliminates the scrap that results from cutting and fitting and the need to provide extra pipe or sanitary tee.

Innovator® Features and Benefits:

- No screws to handle, install, or lose.
- No damage from errant screwdrivers.
- No need to caulk overflow gasket, which is flexible to compensate for the slope and curvature of different tubs.
- No callbacks; eliminates alignment problems and leaks.

Approvals:

- Non-corrugated, flexible PVC tubing.
- Manufactured in compliance with ASME A112.18.2-2005/ CSA B125.2-05; and IAPMO PS 69-2006.

Patents:

https://www.watcomfg.com/patents/

Thread Size:

- 1¹/₂" 11¹/₂ NPSM (Coarse Thread)
- 1.865" Major Diameter (outside thread diameter)
- 11.5 threads per inch

Piping: Schedule 40: ☐ PVC ☐ ABS

ROUGH-IN (RI's) and STOPPER/FACEPLATE (SF's)

